


AccuTrowel

PRODUCT OVERVIEW



AccuTrowel sets are available in 2 sizes:

Full Set: Full Set: 2", 2-1/2", 3", 4", 5", 6", 8", 10", 12"

Short Set: 2", 4", 6" 8", 12"

Glove RG-2400 on the pipe until you cannot see the substrate at all, using the proper trowel size, place the AccuTrowel on the pipe and holding it at a 90 degree angle, slide it down the pipe removing excess from the trowel as required and put it back in the bucket, or on the next section of pipe, repeat the process around the entire pipe. Use a small amount of RG excess build up from the trowel on your finger to smooth out the trowel tracks.

Some imported pipe will come to the job site egg shaped or slightly oval in shape. The AccuTrowel may not fit on these odd-shaped out of spec pipes very well.

- Install ALL RG-2400 products accurately
- · Sets are available in 2 size ranges
- · Save labor
- · Eliminate excess application
- · No guessing about applied thickness
- · Accurate 25 mil thickness
- Measures pipe sizes from 2" to 12"
- · T-304 stainless steel construction













